

TECHSPEC® 50.8mm Dia. x 500.0mm EFL, Uncoated, Concave Laser Mirror



TECHSPEC Uncoated Concave Mirrors

Stock **#11-352** 3-4 DAYS



1



£170.00

ADD TO CART

Qty 1-4

£170.00

Qty 5+

£149.60

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Substrate: ☐ [Fused Silica](#) (Coming 7980)

Surface Quality:
20-10

Diameter (mm):
50.80 +0.00/-0.20

Effective Focal Length EFL (mm): 500.00
Radius of Curvature (mm): 1,000.00
Coating: Uncoated
Back Surface: Fine Grind
Center Thickness CT (mm): 9.68
Clear Aperture (%): 90
Edge Thickness ET (mm): 10.00 ±0.20
Radius R ₁ (mm): 1,000.00
Type: Concave Mirror
Irregularity (P-V) @ 632.8nm: 3λ/20

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View
