

TECHSPEC® 50.8mm Diameter Enhanced Aluminum Coated, λ/10 Mirror



Stock **#39-224** [CONTACT US](#)

- 1 + **£134.30**

ADD TO CART

Qty 1-5
£134.30

Qty 6+
£107.10

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
50.80 +0.00/-0.20

Surface Flatness (P-V):
λ/10 (measured before coating)

Substrate: ☐
[Fused Silica](#) (Corning 7980)

Back Surface: Commercial Polish
Surface Quality: 20-10
Dimensional Tolerance (mm): +0.0/-0.10
Coating Specification: R_{avg} >95% @450 - 650nm
Coating: Enhanced Aluminum (450-650nm)
Coating Type: Metal
Bevel: Protective bevel as needed
Clear Aperture (%): 90
Edges: Ground
Parallelism (arcsec): <180
Thickness (mm): 9.53 ±0.20
Type: Flat Mirror
Wavelength Range (µm): 0.45 - 0.65
Wavelength Range (nm): 450 - 650
Damage Threshold, Reference: 0.2 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant