

**TECHSPEC® 50mm Dia., Nd:YAG Hard Coated OD 4.0 10nm Bandpass Filter Kit (4 Filters)**



Stock #15-099 [CONTACT US](#)

- 1 + **£2,070.60**

ADD TO CART

|           |
|-----------|
| Qty 1+    |
| £2,070.60 |

|                               |
|-------------------------------|
| Volume Pricing                |
| <a href="#">Request Quote</a> |

**!** Prices shown are exclusive of VAT/local taxes

|                       |
|-----------------------|
| Get Product Downloads |
|-----------------------|



|                                                                                                                                                 |
|-------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Diameter (mm):</b><br>50.00                                                                                                                  |
| <b>Optical Density OD (Average):</b><br>≥4.0                                                                                                    |
| <b>Full Width-Half Max FWHM (nm):</b><br>10.00                                                                                                  |
| <b>Filters Included :</b><br>Center Wavelengths: <a href="#">266nm</a> , <a href="#">355nm</a> , <a href="#">532nm</a> , <a href="#">1064nm</a> |

|                                                                                                                                                                            |
|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Coating:</b><br>Hard Coated                                                                                                                                             |
| <b>Type:</b><br>Bandpass Filter                                                                                                                                            |
| <b>Typical Applications:</b><br>Nd:YAG Laser Line Cleanup                                                                                                                  |
| <b>Wavelength:</b><br>Nd:YAG                                                                                                                                               |
| <b>Number of Filters:</b><br>4                                                                                                                                             |
| <b>Environmental Durability:</b><br>Humidity: MIL-STD 810.F, Method 507.4                                                                                                  |
| <b>Physical Durability:</b><br>Adhesion: MIL-C-48497A, 3.4.1.1<br>Abrasion: MIL-C-48497A, 3.4.1.3<br>Temperature: MIL-C-48497A, 3.4.2.1<br>Cleaning: MIL-C-48497A, 3.4.2.2 |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS:</b><br><a href="#">Compliant</a>                  |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |