

TECHSPEC® 50mm Dia. Protected Gold Coated, λ /10 ZERODUR® Mirror



Stock **#39-868** 3-4 DAYS

- 1 + **£204.00**

ADD TO CART

Qty 1-5
£204.00
Qty 6+
£163.20
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
50.00 +0.00/-0.20

Surface Flatness (P-V):
 λ /10 (measured before coating)

Substrate: ☐
ZERODUR®

Back Surface: Commercial Polish
Surface Quality: 20-10
Coating Specification: R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm
Coating: Protected Gold (700-10000nm)
Coating Type: Metal
Bevel: Protective bevel as needed
Clear Aperture (%) : 90
Edges: Ground
Parallelism (arcsec): 30
Thickness (mm): 5.00 ±0.20
Type: Flat Mirror
Wavelength Range (nm): 700 - 10000
Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 0.1
Damage Threshold, Reference: ☐ 0.8 J/cm ² @ 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant