

TECHSPEC[®] 532nm, 50mm Diameter, Raman Edge Filter



Stock #86-259 [CONTACT US](#)

-

1

+

£1,729.75

ADD TO CART

Qty 1-9
£1,729.75
Qty 10+
£1,440.75
Volume Pricing
Request Quote

ⓘ

 Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
50.00 +0.0/-0.1

Angle of Incidence (°):
0 ±2

Optical Density OD (Average):
≥6.0

Cut-On Wavelength (nm): 537.30
Design Wavelength DWL (nm): 532
Substrate:  Fused Silica (Corning 7980)
Coating: Hard Coated
Rejection Wavelength (nm): 430 - 532
Surface Quality: 60-40
Thickness Tolerance (mm): +0.1/-0.1
Transmission (%): >93
Type: Longpass Filter
Transition Width (nm): <5.3
Clear Aperture (%): >80
Durability: Environmental: MIL-STD-810F Physical: MIL-C-48497A
Transmitted Wavefront, RMS: <λ/4 @ 633nm
Mount Thickness (mm): 3.5
Note: Bandwidth (nm): >650
Coating Specification: T _{avg} ≥93% @ 538.9 - 1200nm
Wavelength Range (nm): 430 - 1200
Laser Blocking Wavelength (nm): 532.00

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View