

TECHSPEC®

586nm CWL, 25mm Dia, 20nm Bandwidth, Unmounted OD 6 Fluorescence Bandpass Filter



Stock #18-394 3-4 DAYS

[Additional Bandwidths](#)

- 1 + **£265.20**

ADD TO CART

Qty 1-5

£265.20

Qty 6+

£221.85

Volume Pricing

[Request Quote](#)

! Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00 ±0.1

Angle of Incidence (°):
0 ±5

Bandwidth (nm): 20.00
OD 6 Blocking Wavelength Range (nm): 300 - 561 & 610 - 780
Optical Density OD (Average): ≥6.0
Clear Aperture CA (mm): 22.50
Center Wavelength CWL (nm): 586.00
Full Width-Half Max FWHM (nm): 26.00
Substrate: ☐ Fused Silica (Coming 7980)
Minimum Transmission (%): 93
Coating: Hard Coated
Surface Quality: 60-40
Thickness (mm): 2.00 ±0.1
Type: Bandpass Filter
Blocking Wavelength Range (nm): 250 -1120
Construction: Unmounted
Transmitted Wavefront, RMS: λ/4 (prior to coating)
Compatible Fluorophore: SpectrumOrange™ Emission / SpectrumRed™ Excitation
Environmental Durability: Humidity per MIL-STD-810H, Section 507.6 Temperature per MIL-STD-810H, Section 501.7 and 502.7
Physical Durability: Adhesion per MIL-PRF-13830B, Section C.4.5.12 Moderate abrasion per MIL-PRF-13830B, Section C.4.5.11 Cleaning per MIL-C-48497A Section 4.5.4.2
Bevel: Protective bevel as needed

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant