

[All Products](#) / [Optics](#) / [Optical Assemblies](#) / [Laser Optic Assemblies](#) / [LightPath® Fiber Optic Collimators](#)

[See all 70 Products in Family](#)

LightPath 355110 | 543nm Alignment, 0.40 NA Fiber Collimator w/ FC/APC Connector

See More by [Lightpath®](#)



Fiber Optic Collimator and Focuser Assemblies



Stock **#13-553** [CONTACT US](#)



1



£229.50

ADD TO CART

Qty 1-5

£229.50

Qty 6+

£168.30

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Effective Focal Length EFL (mm):
6.24 @ 780nm

Numerical Aperture NA:
0.40

Substrate: D-ZLaF52LA
Coating: BBAR (350-700nm)
Coating Specification: R _{avg} <0.5% @ 350 - 700nm
Surface Quality: 40-20
Clear Aperture CA (mm): 5.00
f#: 1.25
Bevel: Protective bevel as needed
Connector: FC/APC
Construction: 304L Stainless Steel Housing
Housing Diameter (mm): 11.00
Housing Length (mm): 13.0
Lightpath Lens Code: 355110
Mount: M11 x0.5
Type: Fiber Collimator
Wavelength Range (nm): 350 - 700
Conjugate Distance: Infinite
Lens Included: #87-125
Alignment Wavelength (nm): 543

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant