

TECHSPEC® 5X Cf Objective



#88-353: 5X Cf Objective

Stock #88-353 3-4 DAYS



1



£514.25

ADD TO CART

Qty 1-2

£514.25

Qty 3+

£480.25

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Horizontal Field of View, 2/3" Sensor:
1.76mm

Horizontal Field of View, 1.1" Sensor:
2.82

Focal Length FL (mm):
16.00

Clear Aperture CA (mm): 11.4
Coating: 425 - 675nm BBAR
Length (mm): 97.81
Magnification: 5X
Maximum Diameter (mm): 30
Maximum Sensor Format: 1.1"
Mount: C-Mount
Numerical Aperture NA: 0.150
Type: Fluorite
Resolving Power (μm): 4.44
Depth of Field (μm): 12.00
Aperture (mm): Front: 11.4
Operating Temperature (°C): +10 to +40
Working Distance (mm): 16.2
Weight (g): 101
Note: Magnification can be increased by adding tube length (see table)
Wavelength Range (nm): 400 - 700
Style: Finite Conjugate
Manufacturer: Edmund Optics®
Field Number (mm): 17.6
Tube Length (mm): 50.0
Parfocal Length (mm): 60.01
Immersion Liquid: N/A

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View