

TECHSPEC® 5mm 30R/70T Cube Beamsplitter



Stock **#68-545** 3-4 DAYS

⊖ 1 ⊕

£152.15

ADD TO CART

Qty 1-5
£152.15

Qty 6+
£121.55

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Beam Deviation (arcmin):
±3

Bevel:
Protective bevel as needed

Coating:
λ/4 MgF₂ @ 550nm on Faces
Multilayer Dielectric on Hypotenuse

Construction: Cube
Dimensions (mm): 5.0 x 5.0 x 5.0 ±0.10
Reflection/Transmission Ratio (R/T): 30/70
Reflection/Transmission Tolerance (%): ±5
Substrate: ☐ N-BK7
Surface Quality: 60-40
Type: Standard Beamsplitter
Wavelength Range (nm): 400 - 700
Power (fringes) @ 632.8nm: 1.25
Irregularity (fringes) @ 632.8nm: 0.25

Regulatory Compliance

RoHS 2015: Compliant
Reach 223: Compliant
Certificate of Conformance: View