

TECHSPEC<sup>®</sup> 5mm Dia. x 4mm FL, Uncoated Molded Aspheric Condenser Lens



TECHSPEC Molded Aspheric Condenser Lenses

Stock **#36-163** 3-4 DAYS

[Other Coating Options](#)

-

1

+

£22.95

ADD TO CART

Qty 1-10

£22.95

Qty 11+

£20.40

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):  
5.00 +0.0/-0.2

Effective Focal Length EFL (mm):  
4.00 @ 587.6nm

Numerical Aperture NA:

|                                                                                                                 |
|-----------------------------------------------------------------------------------------------------------------|
| 0.625                                                                                                           |
| <b>Back Focal Length BFL (mm):</b><br>1.45                                                                      |
| <b>Substrate:</b> <input type="checkbox"/><br><a href="#">Liba2000+</a>                                         |
| <b>Focal Length Tolerance (%):</b><br>±5                                                                        |
| <b>Coating:</b><br>Uncoated                                                                                     |
| <b>Centering (arcmin):</b><br>≤25                                                                               |
| <b>Surface Quality:</b><br>Molded Side: 5/3 x0.4; E 0.2<br>Polished Side: 5/3 x0.25; E 0.2                      |
| <b>Clear Aperture CA (mm):</b><br>4.35                                                                          |
| <b>Edge Thickness ET (mm):</b><br>2.14                                                                          |
| <b>Center Thickness CT (mm):</b><br>3.88 ±0.30                                                                  |
| <b>f/#:</b><br>0.8                                                                                              |
| <b>Bevel:</b><br>Protective bevel as needed                                                                     |
| <b>Diameter of Asphere (mm):</b><br>5.00                                                                        |
| <b>Radius R<sub>2</sub> (mm):</b><br>∞                                                                          |
| <b>Shape of Back Surface:</b><br>Plano                                                                          |
| <b>Type:</b><br>Condenser Lens                                                                                  |
| <b>Wavelength Range (nm):</b><br>350 - 2000                                                                     |
| <b>Conjugate Distance:</b><br>Infinite                                                                          |
| <b>Note:</b><br><a href="#">Click here</a> for more information on the ISO 10110 surface quality specification. |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Reach 223:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |