

TECHSPEC[®] 5mm Dia., 2mm Thick, MgF₂ Coated λ/4 N-BK7 Window



Stock #45-574 ☐ In Stock

-

1

+

£55.67

ADD TO CART

Qty 1-5
£55.67
Qty 6+
£44.63
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Abbe Number (v_d):
64.17

Bevel:
Protective as needed

Clear Aperture (%):
90

Clear Aperture CA (mm): 4.50
Diameter (mm): 5.00 +0.0/-0.25
Thickness (mm): 2.00 ±0.20
Coating: MgF₂ (400-700nm)
Coating Specification: R_{avg} ≤1.75% @400 - 700nm
Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 7.1 (-30 to +70°C) 8.3 (+20 to +300°C)
Density (g/cm³): 2.51
Edges: Fine Ground
Index of Refraction n_d: 1.516
Knoop Hardness (kg/mm²): 610
Parallelism (arcmin): <1
Poisson's Ratio: 0.206
Substrate: N-BK7
Surface Flatness (P-V): λ/4
Surface Quality: 60-40
Type: Protective Window
Wavelength Range (nm): 400 - 700
Young's Modulus (GPa): 82
Damage Threshold, Reference: ☐ 10 J/cm² @532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant