


600 Grooves/mm, 30mm Dia., 230nm Polychromator Concave Diffraction Grating

See More by [ZEISS](#)



ZEISS Concave Diffraction Gratings



Stock #11-541 3-4 DAYS



1



£497.25

ADD TO CART

Qty 1+

£497.25

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Groove Density (grooves/mm):
600 ±1

Blaze Wavelength (nm):
230

Diameter (mm):

30.00
Coating: Bare Aluminum
Substrate: ☐ N-BK7
Type: Polychromator
Diffraction Efficiency (%) : ≥70 @ 230nm ≥28 @ 400nm ≥15 @ 600nm
Radius of Curvature (mm): 109.77
Groove Profile: Blazed
Angle of Incidence, α (°): -7.24
Diffraction Angle, β @ 200nm (°): 14.24
Object Distance, l_o @ 200nm: 113.64
Focal Distance, l_b @ 200nm: 104.77
Edge Thickness ET (mm): 8.0
Diffraction Area Diameter (mm): ≥24

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View