



600 x 500mm, $\lambda/2$ Retarder Film (WP280)



Retarder Film with protective film removed



Stock **#14-359** 3-4 DAYS

-

1

+

£297.50

ADD TO CART

Qty 1-10

£297.50

Qty 11+

£268.60

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Design Wavelength DWL (nm):
560

Substrate: [Polymer Film WP280](#)

Length (mm): 600.00
Operating Temperature (°C): -40 to +80
Retardance: λ/2
Dimensions (mm): 600.0 x 500.0
Thickness (mm): 0.06 ±0.006
Transmission (%): >90
Type: Retarder Film
Dimensional Tolerance (mm): +0.0/-2.0
Construction: Polarizing Film
Phase Shift (°): 180
Haze (%): <1
Note: Fast axis is indicated by a black stripe on the protective film. This film should be removed before use.
Wavelength Range (nm): 400 - 700
Heat Resistance (°C x Hours): 80 x 1000
Width (mm): 500.00
Retardation (nm): 280 ±5

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant