

TECHSPEC® 6.0mm Dia. x 25mm FL, VIS 0° Coated, Plano-Convex Lens



Stock **#38-275** 3-4 DAYS

[Other Coating Options](#)

- 1 + **£31.45**

ADD TO CART

Qty 1-9
£31.45
Qty 10+
£28.26
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
6.00 +0.0/-0.025

Effective Focal Length EFL (mm):

25.00 @ 587.6nm
Back Focal Length BFL (mm): 24.04
Coating: VS 0° (425-675nm)
Coating Specification: R _{avg} ≤0.4% @ 425 - 675nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 1.45 ±0.05
Edge Thickness ET (mm): 1.10
Radius R₁ (mm): 12.92
Clear Aperture CA (mm): 5.4
f/#: 4.17
Numerical Aperture NA: 0.12
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 425 - 675
Damage Threshold, Reference: ☐ 5 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant