


63.5mm Dia. x 1mm High Efficiency Window



Stock #39-281 3-4 DAYS

-

1

+

£21.68

ADD TO CART

Qty 1-5
£21.68
Qty 6+
£17.43
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Angle of Incidence (°):
0

Bevel:
Protective as needed

Clear Aperture (%):
≥90

Clear Aperture CA (mm): 57.15
Diameter (mm): 63.50 ±0.76
Thickness (mm): 1.00 ±0.25
Coating: BBAR (425-700nm)
Coating Specification: R _{avg} ≤0.5% @ 425 - 700nm
Edges: Ground
Substrate: Float Glass
Surface Quality: 80-50
Transmission (%): 96.9 Average (typical)
Type: Protective Window
Wavelength Range (nm): 425 - 700

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant