

LightPath 354260 | 633nm Alignment, 0.16 NA Fiber Collimator w/ FC/APC Connector

See More by [Lightpath®](#)



Fiber Optic Collimator and Focuser Assemblies



Stock #13-556 3-4 DAYS



1



£229.50

ADD TO CART

Qty 1-5

£229.50

Qty 6+

£168.30

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Effective Focal Length EFL (mm):
15.29 @ 780nm

Numerical Aperture NA:
0.16

Substrate: D-ZK3
Coating: BBAR (600-1050nm)
Coating Specification: Rabs <1.0% @ 600 - 1050nm
Surface Quality: 40-20
Clear Aperture CA (mm): 5.38
f#: 3.12
Bevel: Protective bevel as needed
Connector: FC/APC
Construction: 304L Stainless Steel Housing
Housing Diameter (mm): 11.00
Housing Length (mm): 20.2
Lightpath Lens Code: 354260
Mount: M11 x0.5
Type: Fiber Collimator
Wavelength Range (nm): 600 - 1050
Conjugate Distance: Infinite
Lens Included: #37-099
Alignment Wavelength (nm): 633

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant