


TECHSPEC® 6.35 x 6.35mm 1064nm 45°, Nd:YAG Laser Line Mirror



TECHSPEC® Nd:YAG Laser Line Mirrors

Stock **#39-651** 3-4 DAYS



1



£107.10

ADD TO CART

Qty 1-5

£107.10

Qty 6+

£94.35

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Surface Quality:
10-5

Type:
Laser Mirror

Parallelism (arcmin):
<3

Clear Aperture (%) : 85
Back Surface: Commercial Polish
Reflection at DWL (%) : 99.8
Coating Specification: R _{abs} >99.8% @ 1064nm R _{avg} >99.5% @ 1046 - 1074nm
Wavelength Range (nm) : 1046 - 1074
Surface Flatness (P-V) : λ/10
Coating Type: Dielectric
Coating: Laser Mirror (1046-1074nm)
Design Wavelength DWL (nm) : 1064
Dimensions (mm) : 6.35 x 6.35 +0.00/-0.10
Thickness (mm) : 3.18 ±0.20
Angle of Incidence (°) : 45
Substrate:  Fused Silica (Corning 7980)
Damage Threshold, Reference:  20 J/cm² @ 1064nm, 20ns, 20Hz

Regulatory Compliance

RoHS 2015: Compliant
REACH 201: Compliant
Certificate of Conformance: View