

660nm Dual Stage Free-Space Optical Isolator



660nm Dual Stage Free-Space Optical Isolator, #35-980

Stock #35-980 3-4 DAYS



1



£2,663.90

ADD TO CART

Qty 1+

£2,663.90

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Clear Aperture CA (mm):
4.7

Design Wavelength DWL (nm):
660

Minimum Transmission (%):
80

Operating Temperature (°C):
+15 to +40

Transmission (%):

90 (typical)
Type: Dual Stage Optical Isolator
Wavelength Range (nm): 640 - 680
Style: Faraday
Damage Threshold, By Design: ☐ 40 W, 4 kW/cm ² @DWL
Typical Isolation at Design Wavelength (dB): 67
Minimum Isolation at Design Wavelength (dB): 60

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View