

6mm Dia. x 12mm FL, Small Diameter Plastic Aspheric Lens



Stock #36-628 ☐ In Stock

-

1

+

£25.50

ADD TO CART

Qty 1-10
£25.50
Qty 11+
£21.25
Volume Pricing
Request Quote

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
6.00 ±0.20

Effective Focal Length EFL (mm):
12.00 @ 550nm

Numerical Aperture NA: 0.25
Back Focal Length BFL (mm): 9.09
Substrate: ☐ Acrylic V825
Focal Length Tolerance (%): ±1.5
Aspheric Design Wavelength (nm): 550
Coating: Uncoated
Surface Quality: 60-40
Clear Aperture CA (mm): 5.00
Edge Thickness ET (mm): 3.23
Center Thickness CT (mm): 4.00 ±0.20
f/#: 2.00
Bevel: Protective bevel as needed
Type: Aspheric Lens
Wavelength Range (nm): 400 - 1500
Conjugate Distance: Infinite

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View