

6mm Focal Length Lens, 1" Sensor Format



6mm Focal Length Lens, 1" Sensor Format, #13-755

Stock #13-755 3-4 DAYS



1



£909.50

ADD TO CART

Qty 1+

£909.50

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Iris Option:
Variable

Length (mm):
56.20

Maximum Diameter (mm):
54.0

Weight (g):
215

Horizontal Field of View, 1" Sensor:

96.8°
Maximum Image Circle (mm): 16.00
TV Distortion (%): <-1.8
Type: Fixed Focal Length Lens
Focal Length FL (mm): 6.00
Maximum Sensor Format: 1"
Working Distance (mm): 100 - ∞
Mount: C-Mount
Aperture (f/#): f/1.8 - f/11
Maximum Distortion (%): < -1.8%
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 240: Contains SVHC(s)