

TECHSPEC® 75mm Dia., 0.50 Numerical Aperture Uncoated, Aspheric Lens



Stock #14-997 3-4 DAYS

[Other Coating Options](#)



1



£629.00

ADD TO CART

Qty 1-5

£629.00

Qty 6+

£503.20

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
75.00 +0.0/-0.1

Effective Focal Length EFL (mm):
75.00 @ 587.6nm

Numerical Aperture NA:

0.50
Back Focal Length BFL (mm): 58.25
Substrate: ☐ N-BK7
Aspheric Design Wavelength (nm): 587.6
Asphere Figure Error, RMS @ 632.8nm: 1.2λ
Coating: Uncoated
Centering (arcmin): ≤5
Surface Quality: 60-40
Clear Aperture CA (mm): 67.5
Edge Thickness ET (mm): 4.99
Center Thickness CT (mm): 25.40 ±0.1
f/#: 1.00
Bevel: Protective bevel as needed
Shape of Back Surface: Plano
Type: Aspheric Lens
Wavelength Range (nm): 350 - 2200
Conjugate Distance: Infinite
Power (diopters): 13.33

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View