

TECHSPEC[®] 76.2 x 89.3mm EFL 45° Protected Gold 100Å Off-Axis Parabolic Mirror



Stock #35-587 3-4 DAYS

[Other Coating Options](#)

-

1

+

£786.25

ADD TO CART

Qty 1-5

£786.25

Qty 6+

£707.63

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Type:
Off-Axis Parabolic Mirror

Diameter (mm):
76.20 +0.00/-0.38

Effective Focal Length EFL (mm):

89.28
Focal Length Tolerance (%) : ±1
Radius of Curvature (mm) : 152.40
Coating : Protected Gold (700-10000nm)
Coating Type : Metal
Coating Specification : R _{avg} ≥94% @ 700 - 800nm R _{avg} ≥97% @ 800 - 2,000nm R _{avg} ≥98% @ 2,000 - 12,000nm
Off-Set Angle (°) : 45
Parent Focal Length PFL (mm) : 76.2
Surface Figure, RMS : 3/4λ
Surface Roughness (Angstroms) : <100 RMS
Wavelength Range (nm) : 700 - 10000
Clear Aperture (%) : 90
Surface Quality : 80-50
Compatible Mounting Plates : #63-375
Substrate : Aluminum 6061-T6
Y Offset (mm) : 63.11
Reflected Wavefront, RMS : 3/2λ

Regulatory Compliance

RoHS 2015 : Compliant
Certificate of Conformance : View
Reach 235 : Compliant