

TECHSPEC[®] 76.2mm Dia., 12.7mm Thick, Fused Silica Uncoated Laser Grade Substrate



TECHSPEC[®] Uncoated Laser Window Substrates

Stock #14-844 3-4 DAYS

⊖

1

⊕

£408.85

ADD TO CART

Qty 1-10

£408.85

Qty 11+

£361.25

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Clear Aperture CA (mm):
68.58

Coating:
Uncoated

Diameter (mm):
76.20 +0.00/-0.10

Substrate: Fused Silica (Corning 7980 0A)
Index of Refraction n_d: 1.458
Surface Quality: 10-5
Thickness (mm): 12.70 ±0.20
Type: Laser Window Substrate
Parallelism (arcmin): <3
Bevel: Protective as needed
Clear Aperture (%): 90
Abbe Number (v_d): 67.8
Back Surface: λ/10
Wavelength Range (nm): 200 - 2200
Surface Flatness (P-V): λ/10
Fused Silica Grade: 7980 0A
Edges: Fine Ground

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View