

TECHSPEC® 76.2 x 76.2mm Protected Silver, 4-6λ Mirror



Stock **#36-057** 3-4 DAYS

- 1 + **£54.82**

ADD TO CART

Qty 1-5
£54.82
Qty 6+
£49.73
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Surface Flatness (P-V):
4 - 6λ

Substrate: ☐
Float Glass

Surface Quality:
60-40

Dimensions (mm):

76.2 x 76.2
Dimensional Tolerance (mm): ±0.25
Coating Specification: R _{avg} >98% @ 450 - 2000nm R _{avg} >98% @ 2000 - 10,000nm
Coating: Protected Silver (450-10000nm)
Coating Type: Metal
Clear Aperture CA (mm): 72.39 x 72.39
Edges: Seamed, 0.5mm Maximum Edge Chip
Thickness (mm): 3.00
Type: Flat Mirror
Wavelength Range (nm): 450 - 10000
Length (mm): 76.20
Width (mm): 76.20
Damage Threshold, By Design: ☐ 0.5 J/cm² @ 532nm & 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant
