


TECHSPEC[®] 76.2mm Corner Cube Prism



N-BK7 Corner Cube Retroreflectors

Stock #43-301 3-4 DAYS

-

1

+

£412.25

ADD TO CART

Qty 1-5

£412.25

Qty 6+

£329.80

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Beam Deviation (arcsec):
3

Coating:
Uncoated

Diameter (mm):
76.20 +0.0/-0.1

Substrate: N-BK7
Height (mm): 57.15
Surface Quality: 60-40
Type: Retroreflector
Bevel: Protective bevel as needed
Clear Aperture (%): 95
Height Tolerance (mm): ±0.25
Image Orientation: Left-Handed
Ray Deviation (°): 180
Wavelength Range (nm): 400 - 2200
Power (fringes) @ 632.8nm: 0.25
Irregularity (fringes) @ 632.8nm: 0.25

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View