

780nm Single Stage Free-Space Optical Isolator



780nm Single Stage Free-Space Optical Isolator, #35-973

Stock **#35-973** 3-4 DAYS

- 1 + **£1,977.10**

ADD TO CART

Qty 1+
£1,977.10

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Clear Aperture CA (mm):
4.7

Design Wavelength DWL (nm):
780

Minimum Transmission (%):
85

Operating Temperature (°C):
+15 to +40

Transmission (%):

92 (typical)
Type: Single Stage Optical Isolator
Wavelength Range (nm): 750 - 810
Style: Faraday
Damage Threshold, By Design: ☐ 40 W, 4 kW/cm ² @DWL
Typical Isolation at Design Wavelength (dB): 43
Minimum Isolation at Design Wavelength (dB): 38

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View

