

LightPath 355110 | 780nm Alignment, 0.40 NA Fiber Collimator w/ SMA Connector

See More by [Lightpath®](#)



Fiber Optic Collimator and Focuser Assemblies



Stock #64-772

☒ In Stock

-

1

+

£153.00

ADD TO CART

Qty 1-10

£153.00

Qty 11+

£134.72

Volume Pricing

[Request Quote](#)

!

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Effective Focal Length EFL (mm):
6.24 @ 780nm

Numerical Aperture NA:
0.40

Substrate: D-ZLaF52LA
Coating: BBAR (600-1050nm)
Coating Specification: R _{abs} <1.0% @ 600 - 1050nm
Surface Quality: 40-20
Clear Aperture CA (mm): 5.00
f/#: 1.25
Bevel: Protective bevel as needed
Connector: SMA
Construction: 304L Stainless Steel Housing
Housing Diameter (mm): 11.00
Housing Length (mm): 13.00
Lightpath Lens Code: 355110
Mount: M11 x0.5
Type: Fiber Collimator
Wavelength Range (nm): 600 - 1050
Conjugate Distance: Infinite
Lens Included: #87-126
Alignment Wavelength (nm): 780

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant