

7mm Dia. x 7.32mm FL, Small Diameter Plastic Aspheric Lens



Stock #15-272 3-4 DAYS

- 1 + **£27.20**

ADD TO CART

Qty 1-10

£27.20

Qty 11+

£22.52

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
7.00 ±0.20

Effective Focal Length EFL (mm):
7.32

Numerical Aperture NA: 0.48
Back Focal Length BFL (mm): 6.58
Substrate: Acrylic V825
Focal Length Tolerance (%): ±1.5
Aspheric Design Wavelength (nm): 550
Coating: Uncoated
Surface Quality: 60-40
Clear Aperture CA (mm): 5.60
Edge Thickness ET (mm): 0.88
Center Thickness CT (mm): 2.10 ±0.20
f/#: 1.05
Type: Aspheric Lens

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View