


TECHSPEC[®] 800nm, 12.7mm Dia., 45° Thin Film Polarizer



TECHSPEC[®] Ultrafast Thin Film Polarizers

Stock #13-054 3-4 DAYS



1



£283.90

ADD TO CART

Qty 1-4

£283.90

Qty 5+

£250.75

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Angle of Incidence (°):
45 ±1

Coating:
Thin Film Dielectric

Design Wavelength DWL (nm):
800

Diameter (mm): 12.70 +0.00/-0.10
Extinction Ratio: 1000:1
Substrate: □ Fused Silica (Corning 7980)
Surface Quality: 10-5
Thickness (mm): 3.00 ±0.10
Type: Linear Polarizer
Parallelism (arcmin): <3
Clear Aperture (%): 85
Transmitted Wavefront, P-V: λ/10 @ 633nm
Coating Specification: S1: R _s >99.8% @ 800nm, T _p >98% @ 800nm S2: R _p <0.1% @ 800nm

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View