

TECHSPEC®

832nm CWL, 25mm Dia, 37nm Bandwidth, Unmounted OD 6 Fluorescence Bandpass Filter



Stock #18-401

3-4 DAYS

Additional Bandwidths



1



£272.85

ADD TO CART

Qty 1-5

£272.85

Qty 6+

£232.05

Volume Pricing

Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):

25.00 ±0.1

Angle of Incidence (°):

0 ±5

Bandwidth (nm): 37.00
OD 6 Blocking Wavelength Range (nm): 550 - 794 & 878 - 1075
Optical Density OD (Average): ≥6.0
Clear Aperture CA (mm): 22.50
Center Wavelength CWL (nm): 832.00
Full Width-Half Max FWHM (nm): 45.00
Substrate: ☐ Fused Silica (Coming 7980)
Minimum Transmission (%): 93
Coating: Hard Coated
Surface Quality: 60-40
Thickness (mm): 2.00 ±0.1
Type: Bandpass Filter
Blocking Wavelength Range (nm): 250 - 1100
Construction: Unmounted
Transmitted Wavefront, RMS: λ/4 (prior to coating)
Compatible Fluorophore: ICG-A Excitation
Environmental Durability: Humidity per ML-STD-810H, Section 507.6 Temperature per ML-STD-810H, Section 501.7 and 502.7
Physical Durability: Adhesion per ML-PRF-13830B, Section C.4.5.12 Moderate abrasion per ML-PRF-13830B, Section C.4.5.11 Cleaning per ML-C-48497A Section 4.5.4.2
Bevel: Protective bevel as needed

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant