

85 x 101mm, 4-6λ Mirror



4-6λ First Surface Mirrors

Stock #32-362 3-4 DAYS

-

1

+

£32.30

ADD TO CART

Qty 1-5
£32.30

Qty 6+
£25.93

Volume Pricing
Request Quote

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Surface Flatness (P-V):
4 - 6λ

Substrate: ☐
Float Glass

Surface Quality:
80-50

Dimensions (mm): 85.0 x 101.0 ±0.76
Coating Specification: R_{avg} >85% @400 - 700nm
Coating: Protected Aluminum (400-700nm)
Coating Type: Metal
Angle of Incidence (°): 45.00
Bevel: Protective as needed
Clear Aperture (%): >90
Thickness (mm): 3.20
Type: Flat Mirror
Wavelength Range (nm): 400 - 700
Length (mm): 101.00
Width (mm): 85.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant