

850nm, 6 x 6mm, OD 2.0 Longpass Filter



OD 2.0 Longpass Filters

Stock #15-207 3-4 DAYS

-

1

+

£38.25

ADD TO CART

Qty 1-9

£38.25

Qty 10+

£34.42

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Dimensions (mm):
6.00 x 6.00 +0.00/-0.20

Angle of Incidence (°):
0

Optical Density OD (Average):
≥2.0

Cut-On Wavelength (nm): 850.00 ±17
Substrate: 
Length (mm): 6.00
Coating: Hard Coated
Rejection Wavelength (nm): 600 - 810
Surface Quality: 60-40
Thickness (mm): 2.00 ±0.10
Transmission (%): ≥85
Transmission Wavelength (nm): 890 - 1600
Type: Longpass Filter
Width (mm): 6.00
Clear Aperture (%): 90
Environmental Durability: ML-STD-810F, Section 507.4
Physical Durability: ML-C-48497A, Section 3.4.1
Wavelength Range (nm): 600 - 1600

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View