


900nm, 25mm Dia., OD 2.0 Shortpass Filter



OD 2.0 Shortpass Filters

Stock **#15-265** 3-4 DAYS

⊖ 1 ⊕ **£88.40**

ADD TO CART

Qty 1-9
£88.40
Qty 10+
£79.56
Volume Pricing
Request Quote

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads	
Diameter (mm): 25.00 +0.00/-0.20	
Angle of Incidence (°): 0	
Optical Density OD (Average): ≥2.0	

Cut-Off Wavelength (nm): 900.00 ±18
Substrate: 
Coating: Hard Coated
Rejection Wavelength (nm): 950 - 1180
Surface Quality: 60-40
Thickness (mm): 2.00 ±0.10
Transmission (%): ≥85
Transmission Wavelength (nm): 500 - 860
Type: Shortpass Filter
Clear Aperture (%): 90
Environmental Durability: ML-STD-810F, Section 507.4
Physical Durability: ML-C-48497A, Section 3.4.1
Wavelength Range (nm): 500 - 1180

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View