


950nm, 12.5mm Dia., OD 2.0 Shortpass Filter



OD 2.0 Shortpass Filters

Stock #15-255 3-4 DAYS

⊖ 1 ⊕ **£69.70**

ADD TO CART

Qty 1-9
£69.70
Qty 10+
£62.73
Volume Pricing
Request Quote

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
12.50 +0.00/-0.20

Angle of Incidence (°):
0

Optical Density OD (Average):
≥2.0

Cut-Off Wavelength (nm): 950.00 ±19
Substrate: 
Coating: Hard Coated
Rejection Wavelength (nm): 1025 - 1250
Surface Quality: 60-40
Thickness (mm): 2.00 ±0.10
Transmission (%): ≥85
Transmission Wavelength (nm): 500 - 900
Type: Shortpass Filter
Clear Aperture (%): 90
Environmental Durability: ML-STD-810F, Section 507.4
Physical Durability: ML-C-48497A, Section 3.4.1
Wavelength Range (nm): 500 - 1250

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View