

TECHSPEC[®] 9mm Dia. x 27mm EFL, UV-VIS Coated, Near UV Achromatic Lens



Stock #35-994 3-4 DAYS

-

1

+

£113.90

ADD TO CART

Qty 1-5

£113.90

Qty 6+

£91.16

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
9.00 +0.0/-0.025

Effective Focal Length EFL (mm):
27.00

Focal Length Tolerance (%): ±1
Back Focal Length BFL (mm): 24.13
Focal Length Specification Wavelength (nm): 405.00
Clear Aperture CA (mm): 8.1
Centering (arcmin): <1
Center Thickness CT (mm): 5.25 ±0.10
Center Thickness CT 1 (mm): 3.75 ±0.05
Center Thickness CT 2 (mm): 1.50 ±0.05
Radius R₁ (mm): 14.60
Radius R₂ (mm): -12.12
Radius R₃ (mm): -40.64
Edge Thickness ET (mm): 4.29
Substrate: ☐ N-FK5 / F2H1
Surface Quality: 40-20
f/#: 3
Numerical Aperture NA: 0.17
Coating: UV-VIS (345-700nm)
Coating Specification: R _{avg} ≤1.5% @ 345 - 700nm
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Bevel: Protective bevel as needed
Type: Achromatic Lens
Wavelength Range (nm): 345 - 700

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 235: Compliant