

Allied Vision Alvium 1800 U-2050m, 1" 20.2MP, USB 3.1 Monochrome Camera (Board Level)

See More by [Allied Vision](#)



Allied Vision Alvium Camera, Board Level (Front)



Stock **#14-901** [CONTACT US](#)

-

1

+

£535.50

ADD TO CART

Qty 1+
£535.50

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Video Output:

USB 3.1 Gen 1

Type:

Monochrome Camera

Manufacturer: Allied Vision
Mounting Threads: No Mounting Threads/Tripod Adapter
Image Buffer: 256KB
Camera Family: Avium
Model Number: 1800 U-2050m
Imaging Sensor: Sony IMX183
Type of Sensor: Progressive Scan CMOS
Type of Shutter: Rolling
Camera Sensor Format: 1"
Resolution (MegaPixels): 20.20
Pixels (H x V): 5,496 x 3,672
Pixel Size, H x V (µm): 2.4 x 2.4
Sensing Area, H x V (mm): 13.1 x 8.8
Frame Rate (fps): 17.00
Pixel Depth: 8/10 bit
Exposure Time: 17µs - 10s
Connector: USB 3.1 Gen 1, Micro-B
Power Supply: Power over USB or via GPIO
Power Consumption (W): 3.2
GPIOs: 4 Programmable TTL GPIOs
Synchronization: Hardware Trigger (GPIO) or Software Trigger
Dimensions (mm): 13 x 26 x 26 (includes connectors)
Weight (g): 15
Mount: N/A
Housing: Board Level
Interface Port Orientation: Back Panel
Dynamic Range (dB): 65
Operating Temperature (°C): -20 to +85 (mainboard temperature)
Storage Temperature (°C): -20 to +85
GPIO Connector Type: 7-pin JST
Machine Vision Standard: USB3 Vision v1.0, GenICam

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant