


TECHSPEC® 9mm Dia x -12mm FL Negative Doublet Lens MgF₂ Coated



Stock **#62-474** 3-4 DAYS

[Other Coating Options](#)

⊖ 1 ⊕ **£60.35**

ADD TO CART

Qty 1-5
£60.35

Qty 6+
£48.24

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
9.00 +0.0/-0.025

Effective Focal Length EFL (mm):
-12.00

Focal Length Tolerance (%):

±1
Back Focal Length BFL (mm): -13.78
Focal Length Specification Wavelength (nm): 587.6
Clear Aperture CA (mm): 8.1
Centering (arcmin): <1
Center Thickness CT (mm): 4.00 ±0.10
Center Thickness CT 1 (mm): 1.50 ±0.05
Center Thickness CT 2 (mm): 2.50 ±0.05
Radius R ₁ (mm): -6.98
Radius R ₂ (mm): 6.98
Radius R ₃ (mm): 23.22
Edge Thickness ET (mm): 5.79
Substrate:  N-BK7 / N-SF5
Surface Quality: 40-20
f/#: 1.33
Numerical Aperture NA: 0.38
Coating: MgF ₂ (400-700nm)
Coating Specification: R _{avg} ≤1.75% @400 - 700nm
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Bevel: Protective bevel as needed
Type: Negative Achromatic Lens
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View