

Allied Vision Prosilica GT2460C 2/3" Color CCD Camera

See More by [Allied Vision](#)



Stock **#13-944** 3-4 DAYS

[Similar Cameras](#)



1



£2,152.20

ADD TO CART

Qty 1+

£2,152.20

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Video Output:
GigE (PoE)

Type:
Color Camera

Manufacturer:
Allied Vision

Mounting Threads:
1/4-20 with Tripod Mount Adapter [#87-412](#)

Image Buffer: 128MB
Camera Family: Prosilica GT
Model Number: GT 2460 C
Imaging Sensor: Sony IMX264
Type of Sensor: Progressive Scan CMOS
Type of Shutter: Global
Camera Sensor Format: 2/3"
Resolution (MegaPixels): 5.10
Pixels (H x V): 2,464 x 2,056
Pixel Size, H x V (µm): 3.45 x 3.45
Sensing Area, H x V (mm): 8.5 x 7.1
Frame Rate (fps): 23.70
Pixel Depth: 8/12 bit
Exposure Time: 48 µs - 85.9s
Connector: GigE, RJ45 with Screw Locks
Power Supply: Power Supply Required and Sold Separately. USA: #15-281 Europe: #15-281 Japan: #15-281 China: #15-281
Power Consumption (W): 3.4 (12VDC External Power Supply) 4.2 (PoE)
GPIOs: 1 opto-isolated input, 2 opto-isolated outputs, 1 non-isolated input, 2 non-isolated outputs
Synchronization: Hardware Trigger (GPIO) or Software Trigger
Dimensions (mm): 70.5 x 53.3 x 33 (excludes connectors and lens mount)
Weight (g): 211
Mount: C-Mount
Housing: Full
Interface Port Orientation: Back Panel
Dynamic Range (dB): 71.7
Operating Temperature (°C): -20 to +65
Storage Temperature (°C): -20 to +70
GPIO Connector Type: 12-pin Hirose (HR10)
Machine Vision Standard: GigE Vision V1.2, GenICam SFNC V1.2.1

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant