

BFS-U3-04S2M-CS USB 3.1 Blackfly® S, Monochrome Camera

See More by [FLIR](#)



FLIR Blackfly® S USB3 Camera (front)



Stock #11-505 3-4 DAYS



1



£306.85

ADD TO CART

Qty 1+

£306.85

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Video Output:

USB 3.1 Gen 1

Type:

Monochrome Camera

Manufacturer: FLIR
Mounting Threads: 1/4-20 with Tripod Mount Adapter #88-210
Image Buffer: 240MB
Camera Family: Blackfly® S
Model Number: BFS-U3-04S2M-CS
Imaging Sensor: Sony IMX287
Type of Sensor: Progressive Scan CMOS
Type of Shutter: Global
Camera Sensor Format: 1/2.9"
Resolution (MegaPixels): 0.40
Pixels (H x V): 720 x 540
Pixel Size, H x V (µm): 6.9 x 6.9
Sensing Area, H x V (mm): 4.97 x 3.73
Frame Rate (fps): 522.00
Pixel Depth: 8/10/12 bit
Exposure Time: 4µs - 30s
Connector: USB 3.1 Gen 1, Micro-B with Screw Locks
Power Supply: Power over USB or via GPIO with #88-063
Power Consumption (W): 3
GPIOs: 1 opto-isolated input, 1 opto-isolated output, 1 non-isolated bi-directional, 1 non-isolated input
Synchronization: Hardware Trigger (GPIO) or Software Trigger
Dimensions (mm): 29 x 29 x 30 (excludes connectors and lens mount)
Weight (g): 36
Mount: CS-Mount
Housing: Full
Interface Port Orientation: Back Panel
Dynamic Range (dB): 74.43
Operating Temperature (°C): 0 to +50
Storage Temperature (°C): -30 to +60
GPIO Connector Type: 6-pin Hirose (HR10)
Machine Vision Standard: USB3 Vision v1.0

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View

