

[All Products](#) / [Cameras](#) / [Gigabit Ethernet Cameras](#) / [Allied Vision Manta PoE Cameras](#)

[See all 36 Products in Family](#)

Allied Vision Manta G-895C Color CMOS PoE Camera

See More by [Allied Vision](#)



Allied Vision Manta PoE Cameras



Stock **#35-899** 3-4 DAYS

[Similar Cameras](#)



1



£1,955.00

ADD TO CART

Qty 1+

£1,955.00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Video Output:
GigE (PoE)

Type:
Color Camera

Manufacturer: Allied Vision
Mounting Threads: ¼-20 with Tripod Mount Adapter #89-996
Image Buffer: 128MB
Camera Family: Manta PoE
Model Number: Manta G-895C
Imaging Sensor: Sony IMX267
Type of Sensor: Progressive Scan CMOS
Type of Shutter: Global
Camera Sensor Format: 1"
Resolution (MegaPixels): 8.95
Pixels (H x V): 4,112 x 2,176
Pixel Size, H x V (µm): 3.45 x 3.45
Sensing Area, H x V (mm): 14.2 x 7.5
Frame Rate (fps): 13.40
Pixel Depth: 12 bit
Exposure Time: Via Software
Connector: GigE, RJ45 with Screw Locks
Power Supply: Power over Ethernet (PoE), via GPIO, or with external power supply
Power Consumption (W): 3 (12VDC External Power Supply) 3.3 (PoE)
GPIOs: 2 opto-isolated inputs, 2 opto-isolated outputs
Synchronization: Hardware Trigger (GPIO) or Software Trigger
Dimensions (mm): 71 × 44 × 29 (excludes connectors and lens mount)
Weight (g): 200
Mount: C-Mount
Housing: Full
Interface Port Orientation: Back Panel
Dynamic Range (dB): 71.9
Operating Temperature (°C): +5 to +45
Storage Temperature (°C): -10 to +70
GPIO Connector Type: 12-pin Hirose (HR10)
Machine Vision Standard: GigE Vision v1.2, GenICam SFNC V1.2.1

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant

