

[All Products](#) / [Cameras](#) / [Gigabit Ethernet Cameras](#) / [Basler ace2 GigE/5GigE Cameras](#)

[See all 52 Products in Family](#)

Basler ace2 a2A5320-7gmBAS Monochrome GigE Basic Camera



Basler ace2 GigE Cameras (Front)



Stock **#16-601** [CONTACT US](#)

[Similar Cameras](#)

[-](#) 1 [+](#)

£1,308.15

ADD TO CART

Qty 1+

£1,308.15

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Video Output:
GigE (PoE)

Type:
Monochrome Camera

Manufacturer:
Basler

Mounting Threads: ¼-20 with Tripod Mount Adapter #16-641
Image Buffer: Not Specified
Camera Family: ace2
Model Number: a2A5320-7gmBAS
Imaging Sensor: Sony IMX542
Type of Sensor: Progressive Scan CMOS
Type of Shutter: Global
Camera Sensor Format: 1.1"
Resolution (MegaPixels): 16.10
Pixels (H x V): 5,320 x 3,032
Pixel Size, H x V (µm): 2.74 x 2.74
Sensing Area, H x V (mm): 14.6 x 8.3
Frame Rate (fps): 7.00
Pixel Depth: 8/10/12 bit
Exposure Time: Freely Programmable
Connector: GigE, RJ45 with Screw Locks
Power Supply: Power over Ethernet (PoE) or via GPIO with #16-644
Power Consumption (W): 3.5
GPIOs: 1 opto-coupled input line, 2 general purpose I/O (GPIO) lines
Synchronization: Hardware Trigger (GPIO), Software Trigger, or Free-Run
Dimensions (mm): 55.5 x 29 x 29 (excludes connectors and lens mount)
Weight (g): <100
Mount: C-Mount
Housing: Full
Interface Port Orientation: Back Panel
Dynamic Range (dB): 70.9
Operating Temperature (°C): -10 to +60
Storage Temperature (°C): -20 to +80
GPIO Connector Type: 6-pin M8
Machine Vision Standard: GigE Vision 2.0, GenICam

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant