

Basler ace acA2040-55um Monochrome USB 3.0 Camera



Stock **#35-921** 3-4 DAYS

[Similar Cameras](#)



1



£594.15

ADD TO CART

Qty 1+

£594.15

Volume Pricing

[Request Quote](#)

 Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Video Output:  
USB 3.0

Type:  
Monochrome Camera

Manufacturer:  
Basler

|                                                                                                               |
|---------------------------------------------------------------------------------------------------------------|
| <b>Mounting Threads:</b><br>¼-20 with Tripod Mount Adapter <a href="#">#88-517</a>                            |
| <b>Image Buffer:</b><br>Not Specified                                                                         |
| <b>Camera Family:</b><br>ace                                                                                  |
| <b>Model Number:</b><br>acA2040-55um                                                                          |
| <b>Imaging Sensor:</b><br>Sony IMX265                                                                         |
| <b>Type of Sensor:</b><br>Progressive Scan CMOS                                                               |
| <b>Type of Shutter:</b><br>Global                                                                             |
| <b>Camera Sensor Format:</b><br>1/1.8"                                                                        |
| <b>Resolution (MegaPixels):</b><br>3.00                                                                       |
| <b>Pixels (H x V):</b><br>2,048 x 1,536                                                                       |
| <b>Pixel Size, H x V (µm):</b><br>3.45 x 3.45                                                                 |
| <b>Sensing Area, H x V (mm):</b><br>7.07 x 5.3                                                                |
| <b>Frame Rate (fps):</b><br>55.00                                                                             |
| <b>Pixel Depth:</b><br>10/12 bit                                                                              |
| <b>Exposure Time:</b><br>Programmable via camera API, hardware trigger                                        |
| <b>Connector:</b><br>USB 3.0, Micro-B with Screw Locks                                                        |
| <b>Power Supply:</b><br>Power over USB                                                                        |
| <b>Power Consumption (W):</b><br>2.6                                                                          |
| <b>GPIOs:</b><br>1 opto-coupled input line, 1 opto-coupled output line,<br>2 general purpose I/O (GPIO) lines |
| <b>Synchronization:</b><br>Hardware Trigger (GPIO), Software Trigger, or Free-Run                             |
| <b>Dimensions (mm):</b><br>29.3 x 29 x 29 (excludes connectors and lens mount)                                |
| <b>Weight (g):</b><br>80                                                                                      |
| <b>Mount:</b><br>C-Mount                                                                                      |
| <b>Housing:</b><br>Full                                                                                       |
| <b>Interface Port Orientation:</b><br>Back Panel                                                              |
| <b>Dynamic Range (dB):</b><br>73.4                                                                            |
| <b>Operating Temperature (°C):</b><br>0 to +50                                                                |
| <b>Storage Temperature (°C):</b><br>-20 to +80                                                                |
| <b>GPIO Connector Type:</b><br>6-pin Hirose (HR10)                                                            |
| <b>Machine Vision Standard:</b><br>USB3 Vision v1.0                                                           |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 235:</b><br><a href="#">Compliant</a>             |