

Coherent® LaserCheck™ 1098293

See More by [Coherent®](#)



Coherent® LaserCheck™, #12-394

Stock **#12-394** ☐ In Stock

-

1

+

£480.25

ADD TO CART

Qty 1+

£480.25

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Active Area Diameter (mm):
8.0

Filters Included :
SCHOTT NG-9, 1 mm thick

Length (inches):
6.59

Type of Optics:
NG-10 Schott ND Filter, 1mm Thickness

Spectral Response (nm): 400 - 1064
Weight (g): 44
Width (inches): 0.92
Depth (inches): 0.78
Power Supply: Battery, Lifetime: 180,000 Samples @ 12 seconds/sample
Type of Sensor: Silicon Cell
Response Time (ms): 2 - 10
Meter Accuracy (%): ±5
Incident Power Density (W/cm²): Without Filter: 0.5 With Filter: 30
Power Resolution (µW): 0.01
Incident Power (mW): Without Filter: 0.005 - 10 With Filter: 0.005 - 1000
Minimum Incident Beam Power (µW): 3 - 10

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View
