


Coherent® OBIS™ FP 1219477 | 488nm LX 100mW Laser, Fiber Pigtail, FC

See More by [Coherent®](#)



Coherent® High Performance OBIS™ Fiber-Pigtailed Laser Systems



Stock **#12-365** [CONTACT US](#)



1



£9,877.00

ADD TO CART

Qty 1+

£9,877.00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Operating Temperature (°C):
10 to 50

Output Power (mW):
100

Polarization:
100:1

Power Stability (%): <2
Spatial Mode: TEM ₀₀
Wavelength (nm): 488.00 ±5
Mode Quality, M²: ≤1.1
Power Supply: Power Supply Required and Sold Separately. USA: #87-473 Europe: #87-473 Japan: #87-473 Korea: Not Available China: #87-473
Warm-Up Time (minutes): <5
Modulation Frequency (MHz): Max Digital: 150
Modulation Frequency (kHz): Max Analog: 500
Pointing Stability (μrad): <5
Output from Fiber: FC/APC; 8° angled
Fiber Cable Type: 3mm Mono-Coil
RMS Noise: ≤0.2% (20Hz to 20MHz)
Manufacturer: Coherent®
Output Type: Fiber-Coupled
Type of Laser: Diode
Laser Class - CDRH: IIIb
Color: Blue
Model Number: 1219477
Fiber Numerical Aperture NA (1/e²): 0.05

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View