


Coherent® OBIS™ FP 1219479 | 520nm LX 25mW Laser, Fiber Pigtail, FC

See More by [Coherent®](#)



Coherent® High Performance OBIS™ Fiber-Pigtailed Laser Systems



Stock #12-369 [CONTACT US](#)

-

1

+

£4,692.00

ADD TO CART

Qty 1+

£4,692.00

Volume Pricing

[Request Quote](#)

!

 Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Operating Temperature (°C):
10 to 50

Output Power (mW):
25

Polarization:
100:1

Power Stability (%): <2
Spatial Mode: TEM ₀₀
Wavelength (nm): 520.00 +10/-0
Mode Quality, M²: ≤1.1
Power Supply: Power Supply Required and Sold Separately. USA: #87-473 Europe: #87-473 Japan: #87-473 Korea: Not Available China: #87-473
Warm-Up Time (minutes): <5
Modulation Frequency (MHz): Max Digital: 100
Modulation Frequency (kHz): Max Analog: 500
Pointing Stability (μrad): <5
Output from Fiber: FC/APC; 8° angled
Fiber Cable Type: 3mm Mono-Coil
RMS Noise: ≤0.25% (20Hz to 20MHz)
Manufacturer: Coherent®
Output Type: Fiber-Coupled
Type of Laser: Diode
Laser Class - CDRH: IIIb
Color: Green
Model Number: 1219479
Fiber Numerical Aperture NA (1/e²): 0.05

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View