

Coherent® PowerMax Pro HP Measurement System 1286588 | 15kW (<10ms burst) 1.5kW (continuous)

See More by [Coherent®](#)



Coherent USB-PowerMax Pro Fast Measurement Systems

Stock **#12-415** [CONTACT US](#)

-

1

+

£2,630.75

ADD TO CART

Qty 1+
£2,630.75

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Model Number:
1286588

Type:
[Meter required](#)

Length of Cable (m):
2.5

Active Area (mm): 25 Dia.
Computer Interface: DB25
Rise Time (μs): ≤10
Calibration Uncertainty (%): ±2
Calibration Wavelength (nm): 810
Spectral Compensation Accuracy (%): ±5
Cooling Method: Water/Air (intermittent)
Maximum Incident Power Density (kW/cm²): 50
Fall Time (μs): ≤10
Compatible Meters: #35-203
Wavelength Range (nm): 700 - 1070, 10600
Power Range (Water-Cooled): 1W to 350W
Maximum Incident Energy Density: 33J/cm² (3ns; 755nm)

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View
