


Coherent® OBIS™ FP 1280766 | 561nm LS 120mW Laser, Fiber Pigtail, FC

See More by [Coherent®](#)



Coherent® High Performance OBIS™ Fiber-Pigtailed Laser Systems



Stock **#12-383** [CONTACT US](#)

-

1

+

£12,597.00

ADD TO CART

Qty 1+

£12,597.00

Volume Pricing

[Request Quote](#)

ⓘ

 Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Operating Temperature (°C):
15 to 40

Output Power (mW):
120

Polarization:
100:1

Power Stability (%): <2
Spatial Mode: TEM ₀₀
Wavelength (nm): 561.00 ±2
Mode Quality, M²: ≤1.1
Power Supply: Power Supply Required and Sold Separately. USA: #87-473 Europe: #87-473 Japan: #87-473 Korea: Not Available China: #87-473
Warm-Up Time (minutes): <5
Modulation Frequency (MHz): Max Digital: 0.05
Modulation Frequency (kHz): Max Analog: 100
Pointing Stability (μrad): <5
Output from Fiber: FC/APC; 8° angled
Fiber Cable Type: 5mm Protective Tubing
RMS Noise: ≤0.25% (20Hz to 20MHz)
Manufacturer: Coherent®
Output Type: Fiber-Coupled
Type of Laser: Diode
Laser Class - CDRH: IIIb
Color: Yellow
Model Number: 1280766
Fiber Numerical Aperture NA (1/e²): 0.06

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View