

TECHSPEC®

Finite Conjugate, UV Coated, 20X/0.33NA RefIX Objective



Stock #39-146

3-4 DAYS

-

1

+

£1,894.65

ADD TO CART

Qty 1+
£1,894.65
Qty 2+
£1,673.65
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Entrance Pupil Position (mm):
7 (Diameter)

Horizontal Field of View, 1/2" Sensor:
0.32mm

Horizontal Field of View, 2/3" Sensor:
0.44mm

Focal Length FL (mm):

9.91
Coating: Enhanced Aluminum (200-11000nm)
Magnification: 20X
Numerical Aperture NA: 0.33
Mounting Threads: RMS
Type: Microscope Objective
Obscuration (%): 30.46
Transmitted Wavefront, RMS: λ/10
Diameter of Small Mirror (mm): 8.4
Working Distance (mm): 18.88
Aperture Diameter (mm): 7.9
Coating Specification: R _{avg} >85% @ 200 - 700nm (typical) R _{avg} >76% @ 700 - 1750nm (typical) R _{avg} >96% @ 1750 - 11000nm (typical)
Wavelength Range (nm): 200 - 11000
Style: Finite Conjugate
Manufacturer: Edmund Optics®
Flange Distance (mm): 150

Regulatory Compliance

RoHS: Not Compliant
Certificate of Conformance: View