

Fly's Eye Array 10 x 10mm, 350µm Pitch, 6.5° Divergence



Microlens Arrays



Stock #12-844 3-4 DAYS



1



£599.25

ADD TO CART

Qty 1-10

£599.25

Qty 11+

£527.00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Effective Focal Length EFL (mm):
1.59

Substrate: [Fused Silica](#) (Corning 7980)

Coating: Uncoated
Type: Flys Eye Lens Array
Wavelength Range (nm): 200 - 2200
Dimensional Tolerance (mm): ±0.05
Dimensions (mm): 10.0 x 10.0
Divergence Angle (°): ±6.5
Lens Profile: Spherical
Pitch (µm): 350.00
Pitch Tolerance (µm): ±0.25
Radius R (mm): 0.73
Thickness (mm): 2.25
Thickness Tolerance (mm): ±0.05
Type of Optics: Double-Convex

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View