

Micro Manual Rotary Stage



Stock **#56-572** ☒ In Stock



1



£366.35

ADD TO CART

Qty 1+

£366.35

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type of Movement:
Rotary

Guide System:
Slide-Fit

Type of Drive:
Fine Screw (80 Pitch)

Type:
English

Stage Size (mm):
25.4 Dia.

Travel (°): 17 (Fine), 360 (Coarse)
Center Hole: 0.275" (7.0mm) Thru with 5/16-24 TPI Thread
Construction: Black Anodized Stage Body with Stainless Steel Thumb Screw
Load Capacity, Normal (kg): 0.23
Mounting Threads: Top: (6) 0-80 on 0.375" (9.5 mm) B.C. Bottom: (6) 0-80 on 0.428" (10.9 mm) B.C.
Note: Coarse Adjustment Tool Included
Stage Size (inches): 1 Dia.
Weight (g): 10
Table Diameter (mm): 19.05 Dia.
Table Diameter (inches): 0.75 Dia.
Travel Per Knob Rotation (μrad): 36.7

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View